


## Type T Glassfibre Insulated Flat Pair thermocouple cable / wire (IEC)



[Click here to view product](#)

<b>Product Code</b>	XE-2363
<b>General Description</b>	Good temperature range but will not prevent ingress of fluids. Fairly flexible but does not provide good mechanical protection.
<b>Cable Length</b>	10m, 25m, 50m, 100m
<b>Cable Type</b>	Flat pair cable
<b>Core / Strands</b>	1/0.315mm
<b>Conductor Cross Section 1/0.315 (mm<sup>2</sup>)</b>	0.078
<b>Outer Colour</b>	Brown & White
<b>+ Colour</b>	Brown

- Colour	White
Drain Wire	No
Insulation Material	Glassfibre insulated
Loop Resistance 1/0.315 (Ohms per combined metre)	6.5
Max. Temperature	+350Å°C (short periods up to 400Å°C)
Min. Temperature	-60Å°C
+ Conductor	Copper
- Conductor	Constantan
Screen	No
Standards Met	Colour code (cores & jacket) to IEC-584-3
Thermocouple Type	T
Tolerance	Class 2