



4 Core PVC Insulated, Tin Plated Copper Screen, PRT Sensor Cable / Wire



[Click here to view product](#)

| | |
|----------------------------|---|
| Product Code | XE-2714 |
| General Description | 4 core PVC insulated 7/0.2mm tin plated copper conductors, twisted cores, polyester tape & nylon cord, tin plated copper braided screen with PVC insulated outer jacket |
| Cable Length | 10, 25, 50m |
| Cable Type | Mylar shield with tin plated copper braiding |
| Core / Strands | 7/0.2mm |
| Insulation Material | PVC insulation |
| Max. Temperature | +105°C |
| Min. Temperature | -10°C |
| Number of Wires | 4 |

| | |
|----------------------|---|
| Standards Met | Cores colour coded 2 x Red / 2 x White to IEC-751 with black outer jacket |
|----------------------|---|

