


Glassfibre insulated ANSI Exposed Junction Thermocouple with Miniature Plug - Types K



[Click here to view product](#)

Product Code	XE-3586
General Description	Fast response, welded exposed junction
Sensor Type	Good temperature resistance (not suitable in fluids)
Thermocouple Type	K
Thermocouple Junction	Exposed
Cable Length	1, 2, 5 or 10 metre
Cable Type	glassfibre insulated flat pair cable
Core / Strands	1/0.3mm conductors
Cable Termination	Miniature Plug
Max. Temperature	+350°C (short periods up to 400°C)

Min. Temperature	?60°C
Tolerance	ANSI MC96.1 Class 2
Standards Met	ANSI MC96.1

