


## Glassfibre insulated ANSI Exposed Junction Thermocouple with Bare Tails - Types K



[Click here to view product](#)

<b>Product Code</b>	XE-3545
<b>General Description</b>	Fast response, welded exposed junction
<b>Sensor Type</b>	Good temperature resistance (not suitable in fluids)
<b>Thermocouple Type</b>	K
<b>Thermocouple Junction</b>	Exposed
<b>Cable Length</b>	1, 2, 5 & 10 metre
<b>Cable Type</b>	glassfibre insulated flat pair cable
<b>Core / Strands</b>	1/0.3mm
<b>Cable Termination</b>	Bare tails
<b>Max. Temperature</b>	+350°C (short periods up to 400°C)

<b>Min. Temperature</b>	?60°C
<b>Tolerance</b>	ANSI MC96.1 Class 2
<b>Standards Met</b>	ANSI MC96.1

