


Self Adhesive Patch PT100 Sensor - Type PRT



[Click here to view product](#)

Product Code	XE-3660
General Description	Suitable for general purpose industrial & commercial use
Sensor Type	Silicone rubber patch with self adhesive foil backing
Element	Pt100
Patch dimensions	L40 x W15mm
Cable Length	2 or 5m
Cable Type	PTFE insulated twisted leads
Core / Strands	7/0.2mm
Cable Termination	Bare Tails
Termination Type	4-wire tails allows connection to any PT100 instrument 2, 3 or 4 wire

Max. Temperature	+150°C
Min. Temperature	-50°C
Accuracy	class B
Number of Wires	4