

# Pt100 Class B Sensors with Teflon insulated lead - Type PRT



[Click here to view product](#)

<b>Product Code</b>	XE-3663
<b>Sensor Type</b>	Pt100 element in a 3.0mm or 4.0mm diameter 316 stainless steel probe
<b>Element</b>	Pt100 element to IEC 751 Class B
<b>Probe Diameter</b>	3.0mm or 4.0mm
<b>Probe Length</b>	from 25mm to 125mm
<b>Sheath Material</b>	316 stainless steel probe
<b>Cable Length</b>	1m
<b>Cable Type</b>	Teflon® insulated twisted lead
<b>Core / Strands</b>	7/0.16mm
<b>Cable Termination</b>	Bare Tails

<b>Max. Temperature</b>	+200°C
<b>Min. Temperature</b>	-50°C
<b>Standards Met</b>	IEC 751
<b>Accuracy</b>	Class B