

## Mica Nozzle Heaters



[Click here to view product](#)

<b>Product Code</b>	XE-9500
<b>General Description</b>	Best quality Mica for high dielectric strength and maximum heat transfer
<b>Element</b>	High performance precision wound element for superior heat distribution
<b>Cable Length</b>	1 metre long stainless steel braided cable
<b>Max. Temperature</b>	Recommended for temperatures up to 300Å°C
<b>Output</b>	240V
<b>Features #1</b>	Full width low expansion straps
<b>Features #2</b>	Specially treated finish to resist oxidation and enhance thermal conductivity
<b>Important Information</b>	Wide range of applications including plastic process machinery, injection / blow moulding, rubber moulding, test equipment, food process industry etc