


## Ceramic Sheathed Pt100 Inserts



[Click here to view product](#)

<b>Product Code</b>	XE-3666
<b>General Description</b>	Pt100 thin film element housed in ceramic sheath
<b>Element</b>	Pt100
<b>Cable Length</b>	50mm or 450mm
<b>Cable Type</b>	PTFE insulated wires
<b>Core / Strands</b>	7/0.15mm
<b>Cable Termination</b>	Bare Tails
<b>Max. Temperature</b>	+250°C
<b>Min. Temperature</b>	-50°C
<b>Tolerance</b>	Class B

<b>Detector Dimensions</b>	Ceramic 5mm dia x 35mm long
<b>Number of Wires</b>	2 or 4

