


## 4 Core Silicone Rubber Insulated, Rounded Section, PRT Sensor Cable / Wire



[Click here to view product](#)

<b>Product Code</b>	XE-2798
<b>General Description</b>	4 core silicone rubber insulated 7/0.2mm tin plated copper conductors, twisted together with silicone rubber outer jacket
<b>Cable Length</b>	10, 25m
<b>Cable Type</b>	Silicone rubber insulated
<b>Core / Strands</b>	7/0.2mm
<b>Insulation Material</b>	Silicone rubber insulated, tin plated copper conductors, twisted together with silicone rubber outer jacket
<b>Max. Temperature</b>	+200°C
<b>Min. Temperature</b>	-40°C

<b>Number of Wires</b>	4
<b>Standards Met</b>	Cores colour coded 2 x Red / 2 x White to IEC-751