


## PFA insulated Twin Twisted IEC Exposed Junction Thermocouple with Miniature Plug - Types K,J,T



[Click here to view product](#)

<b>Product Code</b>	XE-3530
<b>General Description</b>	Fast response, welded exposed junction
<b>Sensor Type</b>	Exposed Junction
<b>Thermocouple Type</b>	K, J & T
<b>Cable Length</b>	1, 2, 5 & 10m
<b>Cable Type</b>	Teflon® PFA insulated twin-twisted lead
<b>Core / Strands</b>	1/0.2mm, 1/0.315mm, 7/0.2mm, 1/0.5mm
<b>Termination Type</b>	Miniature flat pin plug, colour coded in accordance IEC 584
<b>Max. Temperature</b>	+250°C
<b>Min. Temperature</b>	-75°C

<b>Tolerance</b>	Class 1
<b>Standards Met</b>	IEC-584-3
<b>Connector Type</b>	Plug
<b>Connector Size</b>	Miniature