

# GM816 Anemometer Wind Meter Anemometer / Digital Anemometer



[Click here to view product](#)

|                                 |   |
|---------------------------------|---|
| <b>Product Code</b>             | XE-4003-001   |
| <b>Model</b>                    | GM816 Anemometer Wind Meter Anemometer / Digital Anemometer     |
| <b>Accuracy</b>                 | +/- 5%  |
| <b>Air Temp: Accuracy</b>       | +/- 2°C, +/- 3.6F   |
| <b>Air Temp: Range</b>          | -10~45°C, 14~113°F  |
| <b>Air Temp: Resolution</b>     | Resolution 0.2°C, 0.36°F  |
| <b>Air Velocity: Range</b>      | 0.3 - 30m/s, 0 - 90km/h, 0 - 5860ft/min, 0 - 65mph, 0 - 55Knots |
| <b>Air Velocity: Resolution</b> | 0.1m/s, 0.3km/h, 19ft/min, 0.2mph, 0.2Knots                     |
| <b>Air Velocity: Threshold</b>  | 0.1m/s, 0.3km/h, 39ft/min, 0.2mph, 0.1Knots                     |
| <b>Battery</b>                  | 1 x 3V CR2032 battery (Not Included)                            |

|                              |  |
|------------------------------|--|
| <b>Colour</b>                | Yellow / Black                           |
| <b>Current Consumption</b>   | 3mA Approx                               |
| <b>Dimensions</b>            | 10.5 x 4.5 x 2 cm / (4.13 x 1.77 x 0.79) |
| <b>Operating Humidity</b>    | less than or equal to 90%RH              |
| <b>Operating Temperature</b> | -10~45°C (14~113°F)                      |
| <b>Weight</b>                | 105g / 3.7oz                             |
| <b>Storage Temperature</b>   | -40~60°C, -40~140°F                      |
| <b>Thermometer</b>           | NTC Thermometer                          |