

Mineral Insulated Dual Thermocouple with Standard Duplex Type K Plug



[Click here to view product](#)

Product Code	XE-2010
General Description	310 stainless steel sheath. Sheath can be bent/formed to suit many applications and processes.
Sensor Type	Mineral insulated Type ?K? with Duplex Thermocouple Plug
Thermocouple Type	K IEC
Thermocouple Junction	Insulated hot junction
Termination Type	Standard duplex plug termination (200°C)
Max. Temperature	1100°C
Min. Temperature	-40°C
Standards Met	Conforms to IEC 584 specification

Connector Type	Plug
Connector Size	Standard
Length	150, 250 or 500mm