


Bi-Metal Thermometer Temperature Gauges - Back Entry Style with 1/2" BSP Pocket



[Click here to view product](#)

Product Code	XE-0700
Accuracy	Class 1 (1% F.S..D.)
Dial Size	100mm
Construction	Flush fitting bayonet locking case and bezel
Measuring Element	Bi-Metalic coil
Ranges Â°C	-20 to +40°C, 0 to +100°C, 0 to +120°C, 0 to +200°C
Over Limit Range	130% full scale
Stem / Bulb	316 Stainless steel
Case / Bezel ring	Stainless steel AISI 316L
Window	Glass

Dial	Aluminium, black figures on white
Pointer	Aluminium, black
Movement	Direct drive on back entry
Ambient Temperature	-10°C....+50°C
Temperature Effect	max...0,3% / 10°C
Protection EN 60 529	IP65