

## Bi-Metal Thermometer Temperature Gauges - Bottom Entry Style Without Pocket



[Click here to view product](#)

<b>Product Code</b>	XE-0616
<b>Accuracy</b>	Class 1 (1% F.S..D.)
<b>Dial Size</b>	100mm
<b>Construction</b>	Flush fitting bayonet locking case and bezel
<b>Measuring Element</b>	Bi-Metalic coil
<b>Ranges Å°C</b>	-20 to +40°C, 0 to +100°C, 0 to +120°C, 0 to +200°C
<b>Over Limit Range</b>	130% full scale
<b>Stem / Bulb</b>	316 Stainless steel
<b>Case / Bezel ring</b>	Stainless steel AISI 316L
<b>Window</b>	Glass

<b>Dial</b>	Aluminium, black figures on white
<b>Pointer</b>	Aluminium, black
<b>Movement</b>	Direct drive on bottom entry
<b>Ambient Temperature</b>	-10°C....+50°C
<b>Temperature Effect</b>	max...0,3% / 10°C
<b>Protection EN 60 529</b>	IP65