

4-20mA remote wall mounted housing, Pt100 input with PFA or SSOB cable & PRT sensor



[Click here to view product](#)

Product Code	XE-5660
General Description	Compatible with Pt100 platinum resistance thermometers
Sensor Type	Surface Mounting for remote installation
Cable Length	1 or 2 metre
Cable Type	PFA screened or Fiberglass stainless steel overbraid available
Core / Strands	7/0.2mm
Head Type	High Impact ABS Plastic Construction
Thread	Entry Threads M16
Transmitter	Yes
Range	-50°C to +150°C or 0°C to +400°C (either can be re-ranged if desired)

Output	4-20 mA output
---------------	----------------

