


## Pt1000 Class B Sensors with Teflon insulated lead - Type PRT



[Click here to view product](#)

<b>Product Code</b>	XE-3682
<b>General Description</b>	Insulated element in a 4.0mm diameter 316 stainless steel probe
<b>Sensor Type</b>	Pt1000 (1000 Ohms @ 0°C) to IEC 751, Class B
<b>Element</b>	Pt1000
<b>Probe Diameter</b>	4mm
<b>Sheath Material</b>	316 stainless steel probe
<b>Cable Length</b>	1m
<b>Cable Type</b>	Teflon® insulated twisted leads
<b>Cable Termination</b>	Bare Tails
<b>Max. Temperature</b>	+200°C

<b>Min. Temperature</b>	-50°C
<b>Number of Wires</b>	2

