


3 Core PFA Insulated, Tin Plated Copper Screen, PRT Sensor Cable / Wire



[Click here to view product](#)

Product Code	XE-2735
General Description	PFA insulated 7/0.2mm tin plated copper conductors, twisted cores with nylon cord, tin plated copper braided screen with PFA insulated outer jacket
Cable Length	10, 25, 50, 100m
Cable Type	PFA Teflon® construction
Core / Strands	7/0.2mm
Insulation Material	PFA Insulated
Max. Temperature	+260°C
Min. Temperature	-75°C
Number of Wires	3

Standards Met	Cores colour coded Red & White in accordance with IEC-751, black outer jacket
----------------------	---

