

Mineral Insulated Thermocouple with Plain Pot Seal and PFA Insulated ANSI Lead with fitted mini plug - Type K



[Click here to view product](#)

Product Code	XE-0300
General Description	Highly flexible, sheath can be bent/formed to suit many applications and processes
Thermocouple Type	K ANSI
Thermocouple Junction	Insulated hot junction
Probe Diameter	1.0, 1.5, 3.0, 4.5 & 6.0 mm diameters available
Sheath Material	310 stainless steel sheath
Pot Type	Plain pot seal (200°C)
Cable Length	1m
Cable Type	PFA Teflon® insulated flat pair cable and tails (colour coded to ANSI MC96.1)
Core / Strands	7/0.2mm

Cable Termination	Fitted mini plug
Max. Temperature	+1100°C (+750°C for 1.0mm)
Standards Met	Colour coded to ANSI MC96.1