


Adjustable Bayonet Pt100, Glassfibre Stainless Steel Overbraided Cable - Type RTD / PRT



[Click here to view product](#)

Product Code	XE-5654
General Description	PRT with adjustable insertion depth
Sensor Type	Pt100 4 wire
Cable Length	1 or 2 metres
Cable Type	Glassfibre insulated lead with stainless steel Overbraid
Core / Strands	4 core 7/0.2mm
Termination Type	Bare Tails
Max. Temperature	+350°C
Min. Temperature	-50°C
Standards Met	IEC-60751 Class B

Bayonet cap	11.5mm I.D. single slot
Spring	6.0mm diameter x 200mm long