



## IEC Washer Thermocouple, Glassfibre insulated Cable with Stainless Steel Over-Braid Terminating in Bare tails or Standard Plug - Type K



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

## Specifications

<b>General Description</b>	Thermocouple housed in a washer eyelet
<b>Thermocouple Type</b>	K or J
<b>Thermocouple Junction</b>	Grounded tip for quick response
<b>Cable Length</b>	2m
<b>Cable Type</b>	Glassfibre insulated, stainless steel overbraided
<b>Core / Strands</b>	7/0.2mm
<b>Termination Type</b>	Either tails or standard plug termination
<b>Max. Temperature</b>	+350°C
<b>Washer</b>	3.5mm, 4.0mm, 5.0mm, 6.0mm, 8.0mm & 10.0mm clearance hole available