



IEC Washer Thermocouple, Glassfibre insulated Cable with Stainless Steel Over-Braid Terminating in Bare tails or Standard Plug - Type K



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

Specifications

General Description	Thermocouple housed in a washer eyelet
Thermocouple Type	K or J
Thermocouple Junction	Grounded tip for quick response
Cable Length	2m
Cable Type	Glassfibre insulated, stainless steel overbraided
Core / Strands	7/0.2mm
Termination Type	Either tails or standard plug termination
Max. Temperature	+350°C
Washer	3.5mm, 4.0mm, 5.0mm, 6.0mm, 8.0mm & 10.0mm clearance hole available