


## 0.25mm Diameter Fast Response Mineral Insulated Thermocouple with Threaded Pot & PFA IEC Tails - Type K



[Click here to view product](#)

<b>Product Code</b>	XE-0812
<b>General Description</b>	Highly flexible, sheath can be bent/formed to suit many applications and processes
<b>Sensor Type</b>	Type K IEC MD STYLE probes 0.25mm
<b>Thermocouple Junction</b>	Single element, junction insulated or grounded
<b>Probe Length</b>	100mm / 150mm / 250mm
<b>Sheath Material</b>	Stainless steel 316 sheath
<b>Pot Type</b>	M8 x 1.0mm fine pitch threaded pot seal (200°C)
<b>Cable Length</b>	100mm PFA insulated twin twisted IEC - 7/0.2mm
<b>Range</b>	Sensor range -40 to +260°C
<b>Important Information</b>	A 1%+ Length Tolerance applies