

Self Adhesive Patch PT100 Sensor with PFA insulated outer jacket - Type PRT



[Click here to view product](#)

Product Code	XE-3685
Sensor Type	Silicone rubber patch with self adhesive foil backing
Element	Pt100
Patch dimensions	L40 x W15mm x D5mm
Cable Length	1, 3 or 5m
Cable Type	PFA insulated outer jacket
Core / Strands	7/0.1mm
Cable Termination	Bare Tails
Max. Temperature	+150Å°C
Min. Temperature	-50Å°C

Accuracy	Class B
Number of Wires	4