

## Needle Tip Style 80mm



[Click here to view product](#)

<b>Product Code</b>	XE-0040-001
<b>General Description</b>	Flexible sheath can be bent/formed to suit many applications and processes
<b>Sensor Type</b>	Mineral insulated
<b>Thermocouple Type</b>	K
<b>Element/hot junction</b>	Single element, grounded junction offering fast response
<b>Probe Diameter</b>	3.3mm
<b>Probe Length</b>	80mm
<b>Termination Type</b>	Miniature moulded flat pin plug, colour coded ?green? in accordance IEC specification
<b>Max. Temperature</b>	+260°C (Moulded-on plug +110°C)
<b>Min. Temperature</b>	-50°C

<b>Standards Met</b>	IEC
<b>Connector Type</b>	Plug
<b>Connector Size</b>	Miniature (moulded-on)
<b>Probe Material</b>	Needle point tip, 316 stainless steel