

0.75mm Diameter with threaded pot & IEC tails ? Insulated or Grounded



[Click here to view product](#)

Product Code	XE-0188
General Description	Type K with threaded pot & tails in either 316 stainless steel.
Sensor Type	Mineral Insulated
Thermocouple Type	K
Element/hot junction	Single element, junction insulated or grounded from sheath
Probe Diameter	0.75mm
Probe Length	50, 100, 150, 250mm
Sheath Material	316 stainless steel
Pot Type	M8 x 1.0mm fine pitch threaded pot seal (Max Temp 200°C)
Cable Length	100mm

Cable Type	PFA insulated twin twisted IEC (Temp -75 to +250°C)
Core / Strands	7/0.2mm
Termination Type	Bare Tails
Max. Temperature	+750°C
Min. Temperature	-100°C
Tolerance	Class 1
Standards Met	In accordance with IEC 584