

ANSI Washer Thermocouple, Glassfibre insulated Cable with Stainless Steel Over-Braid Terminating in Bare tails or Standard Plug - Type K



[Click here to view product](#)

Product Code	XE-0927
General Description	Thermocouple housed in a washer eyelet
Thermocouple Type	K
Thermocouple Junction	Grounded tip for quick response
Cable Length	2m
Cable Type	Glassfibre insulated, stainless steel overbraided
Core / Strands	7/0.2mm
Termination Type	Either tails or standard plug termination with cable clamps
Max. Temperature	+350°C
Standards Met	ANSI

Washer	3.5mm, 4.0mm, 5.0mm, 6.0mm, 8.0mm & 10.0mm clearance hole available
---------------	---

