

**Washer Thermocouple, Glassfibre insulated  
Cable with Stainless Steel Over-Braid - Type K JIS  
with Standard Plug Termination and 3.5mm  
Washer Hole Size**



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

**Specifications****Specifications**

<b>Product Code</b>	XE-0971-001
<b>General Description</b>	Thermocouple housed in a washer eyelet
<b>Thermocouple Type</b>	K JIS
<b>Thermocouple Junction</b>	Grounded tip for quick response
<b>Cable Length</b>	2m
<b>Cable Type</b>	Glassfibre insulated, stainless steel overbraided
<b>Core / Strands</b>	7/02.mm
<b>Termination Type</b>	Standard plug termination with cable clamps
<b>Max. Temperature</b>	+350°C
<b>Standards Met</b>	JIS (Japanese Industrial Standards)
<b>Washer</b>	3.5mm clearance hole