



## Hermetically Sealed Wire Thermocouple IEC

### Hermetically Sealed Tip



**1.5 x 2.3mm  
Nominal Wire Diameter**

[Click here to view product](#)

|                            |  |
|----------------------------|--|
| <b>Product Code</b>        | XE-6350  |
| <b>General Description</b> | An IP67 wire thermocouple that is hermetically sealed for use in corrosive or wet environments |
| <b>Sensor Type</b>         | Hermetically sealed  |
| <b>Thermocouple Type</b>   | K, J & T   |
| <b>Cable Length</b>        | 1, 2 & 5m  |
| <b>Cable Type</b>          | PFA Flat Pair insulation   |
| <b>Core / Strands</b>      | 7/0.2mm (24 AWG)   |
| <b>Termination Type</b>    | Miniature flat pin plug colour coded in accordance IEC 584 or bare tails                       |
| <b>Max. Temperature</b>    | +260°C   |

|                              |                                       |
|------------------------------|---------------------------------------|
| <b>Min. Temperature</b>      | -75°C                                 |
| <b>Tolerance</b>             | Class 1                               |
| <b>Standards Met</b>         | IEC-584-3                             |
| <b>IP Rating</b>             | IP67                                  |
| <b>Important Information</b> | Pressure tested at 40 PSI as standard |