

## WT635 Wood Moisture Meter



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

This precision meter uses the most advanced microcontroller computer chip core technology. It offers more accurate data, easy operation, and visual readings. With 10 gears for use, it can offer more accurate moisture value.

The WT635 is easy to carry and suitable for measuring the moisture content of wood, bamboo, paper, herbal medicine and other wood fibre items.

There are 8 gears available for wood measurement and 2 gears for building material measurement.

Data hold

Adopt microcomputer (CPU) to make the measurement more accurate.

1000mAh lithium battery

Large LCD display with backlight illumination ensures clear and parallax free readings.

Automatic shutdown after 10 minutes without any operation, or manual shutdown.

Measure the temperature of the environment.

### Specifications

## Specifications

<b>Product Code</b>	XE-4155-001
<b>Model</b>	WT635
<b>General Description</b>	Wood Moisture Meter
<b>Accuracy</b>	+/- 2% on Wood grades 1 to 8
<b>Resolution</b>	+/- 0.5%
<b>Battery</b>	1000mAh 3.7V Lithium Battery
<b>Current Consumption</b>	150mA (no sound)
<b>Dimensions</b>	134mm x 61mm x 25mm
<b>Temperature Range</b>	-9.9°C - 60°C
<b>Power Consumption</b>	DC 2.75 - 3.7V